



REF.	DIMENSIONS		
	Millimeters		
	Min.	Nominal	Max.
A	3.55	4.50	4.90
B	2.34	3.00	3.70
D	2.03	2.70	2.96
E	0.35	0.60	0.70
F	0.25	0.60	1.01
F1	0.70	1.30	1.78
F2	0.70	1.70	1.78
G	4.88	5.00	5.28
G1	2.34	2.50	2.74
H	9.65	10.15	10.67
L	12.70	13.35	14.73
L1	2.93	3.75	6.35
L3	26.90	28.35	31.20
L6	14.22	15.00	16.50
L7	8.30	8.40	9.59
Diam.	3.00	3.20	3.28