



ELECTRICAL :			
IMPEDANCE :	50Ω	50Ω	50Ω
FREQUENCY :	1.0 GHz	2.0 GHz	3.0 GHz
VSWR :	1.1 Max.	1.2 Max.	1.35 Max.

NO	DESCRIPTION	QTY	ITEM NO.	MATERIAL	PLATING
1	BODY	1	SB-321-ROHS	BRASS	NICKEL
2	DIELECTRIC 1	1	T-060002	PTFE	-
3	DIELECTRIC 2	1	T-040008	PTFE	-
4	CENTER PIN	1	SB-321-ROHS	BRASS	GOLD
5	SHELL	1	S-14001-ROHS	BRASS	NICKEL
6	WASHER	1	W-12001-ROHS	BRASS	NICKEL
7	WASHER	1	W-10001	SEE HIGH CARBON STEEL	NICKEL
8	RETAINING RING	1	CW-12001-ROHS	BRASS	NICKEL
9	GASKET	1	G-10001	RUBBER	-

TOP WILLING CO., LT.

編號	SB-321-ROHS	圖號	. \SMA\SB-321-ROHS		版次	A 版
ITEM NO.		DRAWING NO.			EDITION	
電鍍	NGT	日期	2006年10月04日		製圖	Elva
PLATING		DATE			DRAWER	
描述	SMA JACK TO BNC PLUG ADAPTER	單位	mm	比例	設計	
DESCRIPTION		UNIT		SCALE	DESIGN	
		公差	0-0.5mm ± 0.10mm	0.5-8mm ± 0.20mm	認定	
			8-30mm ± 0.40mm	30-120mm ± 0.50mm	APPROVED	

NGT: 1st N is Nickel for body. 2nd G is Gold for pin. 3rd T is PTFE for insulation.