


Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 15895



| No. | Description             | Material    | Treat       | Q'ty |
|-----|-------------------------|-------------|-------------|------|
| 5   | Contact Terminals       | Brass       | Nickel Ptd. | 8    |
| 4   | BP270 Housing           | ABS         |             | 1    |
| 3   | Shield Cover B          | Steel       | Nickel Ptd. | 1    |
| 2   | Shield Cover A          | Steel       | Nickel Ptd. | 1    |
| 1   | YE-115X Shell Cover 6.0 | EVA + LLDPE |             | 1    |

#### Specifications

rating:

100V AC 1A MAX

contact resistance:

pins-30mΩ MAX; shell-50mΩ MAX

Insulation resistance:

MIN 100 MEGΩ @500V DC

voltage withstand:

250V AC R.M.S. for 1 minute

|                |   |                |     |              |             |              |             |                |                 |                    |         |
|----------------|---|----------------|-----|--------------|-------------|--------------|-------------|----------------|-----------------|--------------------|---------|
| 品名<br>ITEM:    | BP270 DIN CABLE PLUG<br>ASSY TYPE (6.0) |                | 製公差 | SHEET:       | 單位<br>unit: | mm           | 日期<br>date: | 07/01/23       | 繪圖<br>drawn by: | DanielShy          |         |
| 料號<br>PART NO: |   | 圖號<br>DRAWING: |     |              |             | 比例<br>scale: | 1:1         | 版本<br>version: | V. 1.0          | 校核<br>approved by: | SkyShyW |
|                |   |                |     | .X +(-)0.25  |             |              |             |                |                 |                    |         |
|                |   |                |     | .2X +(-)0.10 |             |              |             |                |                 |                    |         |