


Rev.	Revision	Date
01	Update	11/4/2010



- ① CABLE:COAXIAL CABLE RG58/U
OD:5.0MM BLACK PVC
- ② CONN:BNC Soldering Lin type
- ③ PVC:PVC 45P BLACK

Test Condition
 (1)high-pressured test:DC 300V
 (2)Insulation impedance:10M Ω
 (3)Leads passes impedance:5.0Ω MAX

P1		P2
1	CORE	1
2	WEAVES	2
Wiring table		

DRAWN	Phoebe	11/4/2010	UNIT: foot	
CHECKED	Sara	11/4/2010		
ENG APPR.			Sinotech	
MFG APPR.				
Q.A.				
GSE 231015			SIZE A4	P/N 169818
			SCALE: 8:1	Weight(kg):
			REV 01	
			SHEET 1 OF 1	