

25 Watts, 120v, 750°F Professional Soldering Iron, 3-wire Cord

◀◀ previous print close next ▶▶

Product Details	
Catalog No.	WP25
UPC Code	037103593597
Type	Temperature Controlled
Wattage	25 W
Temperature Range	750°F
Cord Length	6 ft.
Components Supplied	ST3
Packaging	Peg Hook/Retail Packaging
Tech. Spec.	Solder Safety Warnings.pdf
Lineart	WP25.pdf
Low Res. Image	WP25_100.jpg
High Res. Image	WP25_300.jpg
Stock Item	Normal Stock Item



Package Details (Dimensions)

[Email this Page](#)

Product Features:

- Ideal for a wide variety of electronic tasks, has ST3 soldering tip
- Uses ST series long life double-coated iron-plated tips
- Tip temperature: 750°F
- Quick change knurled collar, stainless steel barrel
- Light blue with cushion grip handle and plug-in heating element
- 6' 3-wire cord, iron is 7 7/8" long
- **IMPORTANT: Use only Weller® tips**
- UL and cUL listed (120 VAC units only)