

Distributed by:



[www.Jameco.com](http://www.Jameco.com) ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.

Jameco Part Number 171408

# SPECIFICATION

CUSTOMER: JAMES

DATE: 10.03.09

MODEL NO: ACU140050

DESIGNED NO: C6951

## 1. APPLICABLE SAFETY STANDARD :

PSE    UL 1310    UL 1950    C-CUL    GS    CE    商檢

## 2. GENERAL APPEARANCE :

- 2.1 THE GENERAL APPEARANCE OF THE AC/DC ADAPTOR SHALL BE WITHOUT DEFORMATION, CRACKS OR CORROSION.  
2.2 THE SHAPE, DIMENSIONS AND MARKINGS OF THE AC/DC ADAPTOR SHALL BE AS SPECIFIED IN THE CONSTRUCTION DRAWING AND NAME PLATE.

## 3. CHARACTERISTICS :

- 3.1 PRIMARY RATED VOLTAGE & LINE FREQUENCY : 120 VAC 60 Hz  
3.2 PRIMARY EXCITING CURRENT (Io) 70 mA MAX. AT INPUT 120 VAC 60 Hz.  
LOADING CURRENT (Ip) X mA MAX. AT INPUT X AC X Hz, LOAD X A.  
3.3 NO - LOAD LOSS : X W MAX. AT INPUT X VAC X Hz.  
3.4 SECONDARY RATED VOLTAGE AND CURRENT :

PRIMARY VOLTAGE	RATE VOLTAGE	TOLERANCE	RATED CURRENT	NO-LOAD VOLTAGE	REGULATION
120VAC 60Hz	14VAC	±5%	500mA-AC		

- 3.5 RIPPLE VOLTAGE : X mV(r.m.s) MAX. AT INPUT X VAC X Hz, LOAD X A.  
3.6 DC RESISTANCE : PRIMARY: X Ω [ X % MEASURED AT 25 °C .  
3.7 HI-POT TEST : AC 1240 V 50/60Hz FOR 1 MINUTES BETWEEN INPUT TO OUTPUT PLUG AND CASE NEED NORMAL PERFORMANCE , LEAKAGE CURRENT 1 mA.  
3.8 INSULATION RESISTANCE : 500 VDC 100 MΩ MIN. BETWEEN INPUT TO OUTPUT PLUG AND CASE.  
3.9 TEMPERATURE RISE :INPUT 120 VAC 60 Hz, OUTPUT LOAD 0.5 A FOR INPUT COIL 75 °C MAX (BY USE RESISTANCE METHOD) ON CASE SURFACE X °C MAX (BY USE THERMOMETER METHOD) AT 25°C AMBIENT.  
3.10 HUMIDITY TEST : TEMP. 40~2 °C, 90-95 % R.H FOR 4 HOURS , AFTER AT MINUTES TAKEN OUT FROM OVEN . AND WIPED DRY. TEST 3.4 、 3.7 AND INSULATION TEST 10 MΩ MIN.

## 4. MECHANICAL PERFORMANCE :

- 4.1 STRAIN-RELIEF TEST : 10 LB FOR 60 SEC. IN ANY DIRECTION .  
4.2 DROP TEST : UNIT IS TO BE DROPPED FROM 3 FEET HIGH ONTO A CONCRETE FLOOR COVERED WITH 1/8 INCH VINYL TILE 3 TIMES, THE UNIT SHOULD MEET THE ITEM 3.7 、 3.8.  
4.3 BENDING RELIEF TEST : THE CORD AND S/R SHALL WITHSTAND WEIGHT OFF 200 g, IT SWINGS FROM LEFT TO RIGHT AT AN ANGLE OF 120 deg , 300 CYCLE TIMES NIN.  
4.4 VIBRATION RESISTANCE : PRODUCT PACKAGED IN A INTENDED MANNER SHALL DEVELOP NO MECHANICAL OR ELECTRICAL FAILURE WHEN SUBJECTED TO A 1.5 mm PEAK TO PEAK AMPLITUDE , 10-50-10 Hz , VIBRATION IN EACH OF X , Y AND Z DIRECTIONS FOR 30 MINUTES .

## 5. TEMPERATURE RANGE:

- 5.1 USE TEMPERATURE EXTENT : 0 °C ~ +40 °C  
5.2 STORAGE TEMPERATURE EXTENT : -25 °C ~ +55 °C

APPROVED BY \_\_\_\_\_ CHECKED BY \_\_\_\_\_ TESTED BY 李淑華

# ELECTRICAL DATA

CUSTOMER: JAMES  
 MODEL NO: ACU140050


DATE: 10.03.09  
 DESIGNED NO: C6951


ITEM	SPEC.	SAMPLE												
		1	2	3	4	5	6	7	8	9	10			
PRIMARY EXCITING CURRENT INPUT 120 V-AC 60 Hz	70 mA MAX.	34												
PRIMARY LOAD CURRENT INPUT 120 V-AC 60 Hz	mA	86												
SECONDARY #1 NO LOAD AC VOLTAGE		17.48												
SECONDARY #1 AC VOLTAGE LOAD 500mA-AC	14V±5%	14.03												
TEMP RISE AFTER 4 HRS WARM UP IN 25 °C AMBIENT	75 °C MAX.	OK												
HI-POT TEST	PRI. TO SEC. & CORE AC 1240 V	OK												



APPROVED BY \_\_\_\_\_ CHECKED BY \_\_\_\_\_ TESTED BY 李淑華

聯輝電機股份有限公司






# 聯輝電機股份有限公司

No	DESCRIPTION	MATERIAL	SPEC. & Q'T	MANUFACTURE
1	Enclosure	Noryl SE100(E455587(B))		East Tung Jung Plastic Haroware Co., Ltd. Jong Wenn Enterprise Co., Ltd.
2	Primary Blades	Nickel Plating		Shin Chuan Electronic & Metal(Hui Zhou) Co., Ltd.
3	Enamelled Wire	Polyurethane Enameled Copper Wire(E85640(S))		Hung Cheng Electric Wire Co., Ltd.
4	Primary Outerwarp	Polyesteer Film Tape (E81174)	0.05mm (4T)	Chyun Yih Tape Co., Ltd. Jeou Uei Co., Ltd.
5	Secondary Outerwarp	Polyesteer Film Tape (E81174)	0.025mm (2T)	Chyun Yih Tape Co., Ltd. Jeou Uei Co., Ltd.
6	Nameplate	P.V.C (MH26173(N))	0.35mm	Koan Hao Enterprise Co., Ltd.
7	Core	Silicon Steel	0.5mm	Top Silicon Steel Corp.
8	Bobbin	Zytel 101 NY66 (E41938)		East Tung Jung Plastic Haroware Co., Ltd. Jong Wenn Enterprise Co., Ltd.
9	Output Cord	Flexible Cord	AWG#24	Huan Wei Enterprise Co., Ltd. Ming Sheng Enterprise Co., Ltd.
10	Thermal Cutoff	M20 or A2(E422267N)	115°C	Joint Force Metal Research & Co.

# 聯輝電機股份有限公司




- 1.尺寸:83x52x78m/m No.3      2.磅數: 400 磅  
 3.印刷:白底藍色字体及圖案      色號: PMS 300

出圖章

名稱	小紙盒	5						
料號		4						
發行日		3						
核准	品保審核	製圖	2					
		李淑華	1					
		符號	日期	變更事項			修訂者	審核者
		單位:m/m	版次	圖號	CN-411			

# 聯輝電機股份有限公司



- 1.材質: PVC
- 2.厚度:0.35 +0.2/-0.1
- 3.印刷:銀底黑字

出圖章	名稱	銘牌	5				
	料號		4				
	發行日		3				
	核准	品保審核	製圖	2			
			李淑華	1			
				符號	日期	變更事項	
			單位:m/m	版次	1-0	圖號	