

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1716861

Dialight

559 Series

5V & 12V - Integral Resistor Snap-in LED - .250" Mounting Hole Panel Mount Indicators



FEATURES / BENEFITS

- ▲ RoHS Compliant
- ▲ Long life - typically 100K hours
- ▲ Low power consumption - uses up to 90% less energy than an incandescent indicator
- ▲ Front panel snap-in mounting requires no additional hardware
- ▲ No heat generated
- ▲ Resistant to shock and vibration
- ▲ Termination - straight terminals for wire wrapping or lead wire for soldering or optional terminals
- ▲ Colors include - red, green, yellow

APPLICATIONS


Dialight's 559 series LED panel mount indicator is available with a variety of LEDs including AlInGaP and InGaN technology for high brightness applications, bicolor and integral resistors. These indicators are designed for a variety of applications such as:

- Main and remote power indication
- Maintenance and warning indication
- Status indication
- Instrumentation
-and many more!

SPECIFICATIONS

- ▲ Voltage requirements:
5 & 12 VDC (no resistor required)
- ▲ Mounting hole size: 0.249 -0.252" (6.32 - 6.40 mm)
- ▲ Panel thickness: 0.031-0.062" (.787 - 1.57 mm)
- ▲ Housing: Black housing material meets UL94V-0 and enhances LED contrast
- ▲ *Operating temperature: -20°C to +85°C
- ▲ *Storage temperature: -55°C to +100°C
- ▲ Electrical connection
Straight terminals for wire wrapping or either 6 or 14 inch 24 AWG lead wire


STRAIGHT TERMINALS - TERMINATION OPTION 001



Dimensions in inches [mm]

NOTE: WIRE LEAD COLOR RED (ANODE) AND BLACK (CATHODE)

**24 AWG 6" WIRE LEADS - TERMINATION OPTION 003 **24 AWG 14" WIRE LEADS - TERMINATION OPTION 007



* Based on LED color - Contact factory for details

Dialight reserves the right to make changes at any time in order to supply the best product possible.

Please see back of page for part numbers and additional specifications.

Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com



MDEL559SIIR001_A



559 Series

5V & 12V - Integral Resistor

Snap-in LED - .250" Mounting Hole

Panel Mount Indicators

5 VOLT OPERATION

Part Number	Color	Peak Wavelength (nm)	Intensity typ. (mcd)	Voltage (VDC)	Current (mA)	Viewing Angle 2Ø 1/2	Maximum DC forward Voltage	Termination	RoHS Complaint
559-0102-001F	Red	635	8	5	10	60	7.5	Straight terminals	✓
559-0202-001F	Green	565	8	5	10	60	7.5	Straight terminals	✓
559-0302-001F	Yellow	583	8	5	10	60	7.5	Straight terminals	✓
559-0102-003F	Red	635	8	5	10	60	7.5	6 inch wire leads	✓
559-0202-003F	Green	565	8	5	10	60	7.5	6 inch wire leads	✓
559-0302-003F	Yellow	583	8	5	10	60	7.5	6 inch wire leads	✓
559-0102-007F	Red	635	8	5	10	60	7.5	14 inch wire leads	✓
559-0202-007F	Green	565	8	5	10	60	7.5	14 inch wire leads	✓
559-0302-007F	Yellow	583	8	5	10	60	7.5	14 inch wire leads	✓

Typical Operating Characteristics (Ta=25°C)

12 VOLT OPERATION

Part Number	Color	Peak Wavelength (nm)	Intensity typ. (mcd)	Voltage (VDC)	Current (mA)	Viewing Angle 2Ø 1/2	Maximum DC forward Voltage	Termination	RoHS Complaint
559-0103-001F	Red	635	8	12	13	60	15	Straight terminals	✓
559-0203-001F	Green	565	8	12	13	60	15	Straight terminals	✓
559-0303-001F	Yellow	583	8	12	13	60	15	Straight terminals	✓
559-0103-003F	Red	635	8	12	13	60	15	6 inch wire leads	✓
559-0203-003F	Green	565	8	12	13	60	15	6 inch wire leads	✓
559-0303-003F	Yellow	583	8	12	13	60	15	6 inch wire leads	✓
559-0103-007F	Red	635	8	12	13	60	15	14 inch wire leads	✓
559-0203-007F	Green	565	8	12	13	60	15	14 inch wire leads	✓
559-0303-007F	Yellow	583	8	12	13	60	15	14 inch wire leads	✓

Typical Operating Characteristics (Ta=25°C)

LED Panel Mount Indicator Selection

Dialight's line of LED Panel Mount Indicators are available in a variety of sizes and options.

Please visit our website for more information.

www.dialight.com

- ▶ .156" (3.96mm) *558 Series*
- ▶ .250" (6.35mm) *559 Series*
- ▶ 5mm *605 Series*
- ▶ 6mm *606 Series*
- ▶ 7mm *607 Series*
- ▶ 8mm *608 Series*
- ▶ 9mm *609 Series*
- ▶ 10mm *610 Series*
- ▶ 11/16" Watertight *557 Series*
- ▶ 1" Watertight *556 Series*

Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com



MDEL559SIIR001_A