

Distributed by:

JAMECO[®]
ELECTRONICS


www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1716895



Holder / No. 560

PC Mount, for TR5®/TE5® Fuses



"A"	code	height
3.0 mm		13
4.3 mm		10

Holes in PCB



Specifications

Packaging

- 1 bulk (1000 pcs.)
- 0 bulk (500 pcs.)

Order Number

- Holder No. 560 0000 13 1
- Holder No. 560 0000 10 0
- Holder No. 560 0000 10 1

Mounting

PC Board, 5.08 mm pin spacing

Materials

- Holder: Thermoplastic, UL 94 V-0
Polyester PCT
- Metal parts: Copper alloy; solderable tinned

Electrical Data (23 °C)

- Rated Voltage: 250 V
- Max. Current/Power: 6.3 A/1.6 W

Soldering Heat Resistance

max. 280 °C, 10 s (Wave)

Minimum Cross Section

Conducting path - 0.1 mm²

Unit Weight

0.4 g



Order Information

Qty.	Order-Number	Series		code height	Packaging
		560	0000		

Specifications are subject to change without notice

Note: 1.00 means the number one with two decimal places. 1,000 means the number one thousand.