


NO.	ITEM	SPECIFICATION
1	Rated Voltage(VDC)	12
2	No Load speed(RPM)	3000± %15
3	No Load Current(A)	0.030Max
4	Rated Speed(RPM)	2400± 12%
5	Rated Current (mA)	60± 14
6	Torque(g.cm)	23.26

Rev.	Revision	Date
01	Update	3/14/2011



NOTE:  
 1. END PLAY:0.05-0.50mm.  
 2.ALL UNSPECIFIED DIMENSION TOLERANCE WILL BE  $\pm 0.10$  mm.

DRAWN	Alex	3/14/2011	UNIT: mm	
CHECKED	Sara	3/14/2011		
ENG APPR.				
MFG APPR.			Sinotech	
Q.A.				
RF-370CH-10670-19.5			SIZE A4	P/N 174693
			SCALE: 2.5:1	Weight(kg):
			REV 01	
			SHEET 1 OF 1	