



P1,P2: M-Y938A  
M-938A

Customer No: No.1



\*NOTE: ALL relevant materials complied with RoHS directive

3	MOLDED PE COLOR TRANSPARENT		M280
	MOLDED PVC BLACK		M304
2	RG58A/U 21AWG STRANDED , BRAID 48, OD 5.0mm, JACKET BLACK DRAWING NO. ECBS2101T-074	3020mm	M304
1	BNC MALE CONNECOR, GOLD FLASH ON CONTACTS, WHITE INSULATOR	2	M98
No.	DESCRIPTION	Q'TY	Supplier

APPROVED		<b>MSL ENTERPRISES CORP.</b>	Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm
CHECKED	HU		
DRAWING	CHEN		

DATE	14/APR/09	ITEM NO.	10X1-01110	UNIT:mm		
------	-----------	----------	------------	---------	--	--

CHECKED