



FEATURES:

- ✓ Mounts in panels from .070" to .375" (1.60mm to 9.53mm).

MATERIALS:

- Banana Jack: Bright Tin Plated Brass
- Mounting Base: Polycarbonate
- Insulator: Polycarbonate
- Lockwasher: Nickel Plated Steel
- Hex Nut: 3/8" 1/4-32 Nickel Plated Brass
- Solder Turret: Bright Tin Plated Brass

RATINGS:

- Operating Voltage: Hands free usage in controlled voltage environments: 2500 Vrms maximum. *For CE compliance:* not intended for hand-held use at voltages above 33 Vrms/70 Vdc.
- Operating Temperature: +239°F (+115°C) Max.
- Current: 15 Amperes

ORDERING INFORMATION:
 Model 2269-0 (Black Base)
 Model 2269-2 (Red Base)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies.