

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1834381


MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

**MINIATURE PRECISION
LIMIT SWITCH**

CATALOG LISTING

914CE18-Q



914CE18-Q

M

DRAWING
NUMBER

1

ISSUE



REPLACES

RELEASE NO. CO-69061


CHECK

REVISIONS

CHECK



Ø.280 STAINLESS
STEEL PLUNGER




NOTES
1 - ZINC HOUSING FINISHED WITH GRAY PAINT

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	FULL	DO NOT SCALE PRINT
		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
OPERATING FORCE — — — — 5 LB MAX	CONTACT ARRANGEMENT S P D T 5A - 250 VAC 1/10HP - 125 OR 250 VAC 	ONE PLACE (.0)	±.030	
DIFFERENTIAL TRAVEL — — — .004 MAX		TWO PLACE (.00)	±.015	
OVERTRAVEL — — — — .118 MIN		THREE PLACE (.000)	±.005	
		ANGLES	±	
		WEIGHT		

DDM/CAD

DRAWN

S A V 11 OCT 91