

100 Watt, 120v, 700°F Heavy Duty Soldering Iron with CT6F7 Tip

◀◀ previous print close next ▶▶

Product Details	
Catalog No.	W100PG
UPC Code	037103474261
Type	Temperature Controlled
Wattage	100 W
Temperature Range	600°F / 700°F / 800°F
Cord Length	6 ft.
Components Supplied	CT6F7
Packaging	Peg Hook/Retail Packaging
Tech. Spec.	Solder Safety Warnings.pdf
Low Res. Image	W100PG_100.jpg
High Res. Image	W100PG_300.jpg
Stock Item	Normal Stock Item



Package Details (Dimensions)

[Email this Page](#)

Product Features:

- Uses Weller "closed loop" method of controlling maximum tip temperature
- Portable line voltage iron - no base station required
- Stainless steel modular plug-in heater, greater efficiency & versatility
- Temperature is controlled by tip-600°F, 700°F, and 800°F tips available
- Nominal heat-up time with 700°F tip is 110 seconds
- Fume extraction adapter kit available - Cat. No. AKFE11
- Uses CT series tips
- Heating element type: Nichrome wound, plug in
- UL and cUL listed