

NO.	SPECIFICATIONS
1	13" long including tip
2	Durable corrosion resistant plastic construction
3	Corrosion treated springs
4	Insulated vacuum pulse
5	Regulated return (1 millisecond \pm 30 %)
6	Uniform reset pressure (11 in. lbs. \pm 20 %)
7	Cushioned shock reduction

Rev.	Revision	Date
01	Update	10/11/2010



DRAWN	Alex	10/11/2010	UNIT: mm		
CHECKED	Sara	10/11/2010			
ENG APPR.			Sinotech		
MFG APPR.					
Q.A.					
KET-HB-017			SIZE A4	DWG.NO. 1942139	REV 01
			SCALE:	Weight(Lbs): 2.0	SHEET 1 OF 1