

## Powered Breadboard: PBB-4060B



### Specifications:

1. Input Power 110V AC or 220VAC @ 50-60Hz +/-10%, international 110/220 VAC switchable.
2. Triple-Output Power Supply: Fixed +5V @ 1.5A, Continuously adjustable 0 ~ +16V @ 500mA and 0 ~ -16V @ 500mA. Accuracy @ +/-5%.
3. Grounded Case
4. Overload and Short Circuit protection
5. Fuse protection
6. Solderless breadboard with 2390 tie points
7. Power switch with light
8. Lead-free circuit board
9. Size: 10 1/4" x 8 3/4" x 3 1/4"
10. Weight: 6 lbs