

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1966843

- Home
- Part Number Search
- Document Search
- CAD Model Search
- Text Search
- Alternate/Lead Free Part Search
- Multiple Part Comparison
- Alphabetical Search
- Brand Search
- Industry Product Search
- Product Type Search
- Product Family Search
- Competitor Cross Reference
- Lead Free Solutions
- Tool Search
- Help/Glossary

Ribbon Cable Connector System (AMP-LATCH)

Ribbon Cable Connectors (AMP-LATCH)

AMP **2-746610-5** Active [Active](#)

RoHS Compliant [RoHS Compliant](#)

(Tyco Electronics P/N: 2-746610-5)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<input type="checkbox"/> General Info <input type="checkbox"/> Sales Info	<input type="checkbox"/> Pricing	<input type="checkbox"/> Tooling
<input type="checkbox"/> Assembly Subcontractors	<input type="checkbox"/> Product Availability	

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Process:	Wave solder capable to 240°C, Wave solder capable to 265°C
Connector Type:	DIP (Dual In Line Package)
No. of Positions:	64
Gender:	Plug
Mating Polarization:	No
Terminate To:	Printed Circuit Board
Mounting Ears:	Without
Contact Mating Area Plating:	Bright Tin over Nickel
Contact Termination Area Plating:	Bright Tin over Nickel
Special PCB Retention:	No
Cable Stop:	Without

Other Properties:	
RoHS/ELV Compliance History:	Always was compliant
Centerline, Matrix (mm [in]):	2.54 x 2.54 [.100 x .100]
With Cover Preassembled:	Yes
Contact Material:	Phosphor Bronze
Housing Material:	Thermoplastic
Housing Flammability Rating:	UL 94V-0
Housing Color:	Black
Special PCB Retention Method:	Kinked Leg Post

Mating Connector Lock:	Without
Strain Relief:	Without

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)

i2 Technologies US, Inc.

HTML Pages converted to PDF Document

This document contain component information from the manufacturer's website which are not available in a revision controlled document from the manufacturer. To facilitate the addition of these parts into the Electronics Database, we are converting the HTML pages related to that part, from the manufacturer's website into Adobe PDF format. The contents of this document is based on the information provided on the manufacturer's website, therefore the information may have been changed by the manufacturer since this was created.

