

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 1967221


### Spare Wire Caps and Tooling

**Material:**


Copper Tin plated

Insulation — Nylon

For  
Unstripped  
Wire



For  
Stripped  
Wire



Wire Size [mm <sup>2</sup> ] Circular Mils	Style	Dimension L Max.	Cap Insulation Color	Wire Insulation Diameter Range	Wire Insulation Diameter Max.	Part Numbers		Tooling	
						Loose Piece	Hand Tool	T-Head	Die For 69875
—	Unstripped Wire	.515 13.08	Yellow	.150-.220 3.81-5.59	—	324487	46063	—	—
22-18 [0.3-0.8.5] 509-3,248	Stripped Wire	.430 10.92	Red	—	.124 3.15	328307*	47386 <sup>1</sup>	59250	—
16-14 [1.4-2.0] 2,050-5,180	Stripped Wire	.430 10.92	Blue	—	.149 3.78	328308*	47387 <sup>1</sup>	59250	68169-1
12-10 [3.0-6.0] 5,180-13,100	Stripped Wire	.478 12.14	Yellow	—	.210 5.33	328309*	59239-4 <sup>2</sup>	—	—
—	Unstripped Wire	.515 13.08	Trans.	.048-.075 1.22-1.91	—	324693 <sup>3</sup>	46063	—	—
			Blue	.120-.145 3.05-3.68	—	324695 <sup>3</sup>	46063	—	—

<sup>1</sup> Long Handle Tool

<sup>2</sup> Heavy Head Tool

<sup>3</sup> Moisture resistant

\*See Table I

**Table I: Military Cross Reference (meets MIL-T-7928)**

Part Number	Military		Part Number
	Dash	Class	
MS 25274	-2	1 & 2	328307
	-3	1 & 2	328308
		2	2-328308-1
	-4	1 & 2	328309

For additional tooling information, consult Technical Support Center at 1-800-722-1111

For complete product information, order Catalog 65472