


Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1975424



- [Home](#)
- [Part Number Search](#)
- [Document Search](#)
- [CAD Model Search](#)
- [Text Search](#)
- [Alternate/Lead Free Part Search](#)
- [Multiple Part Comparison](#)
- [Alphabetical Search](#)
- [Brand Search](#)
- [Industry Product Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Competitor Cross Reference](#)
- [Lead Free Solutions](#)
- [Tool Search](#)
- [Help/Glossary](#)

Soft Shell Connectors

.200" Centerline, 250 V, 13 A max. (Commercial MATE-N-LOK)

AMP **60617-5** Active [Active](#)

RoHS Compliant [RoHS Compliant](#)

(Tyco Electronics P/N: 60617-5)

[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<input type="checkbox"/> General Info <input type="checkbox"/> Sales Info	<input type="checkbox"/> Pricing	<input type="checkbox"/> Tooling
<input type="checkbox"/> Assembly Subcontractors	<input type="checkbox"/> Product Availability	

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Process:	Not relevant for lead free process
Product Type:	Contact
Contact Diameter (mm [in]):	2.13 [0.084]
Packaging Method:	Loose Piece

Other Properties:	
RoHS/ELV Compliance History:	Always was compliant
Connector Line:	Commercial MATE-N-LOK
Contact Termination Area Plating:	Gold (30)
Stock Thickness (mm [in]):	0.30 [0.012]
Voltage (VAC):	250
Current Rating (Amps.):	13

Contact Type:	Socket
Wire Range (mm [AWG]):	0.20-0.80 ² [24-18]
Contact Material:	Brass
Wire Insulation Diameter (mm [in]):	1.52 – 2.54 [0.060 – 0.100]

Comment:

Extraction Tools: Pins- No. 1-305183-1 (IS 7158); Sockets- No. 1-305183-2 (IS 7158); Pins and Sockets-No. 465644-1 (IS 7211).
Insertion Tools: No. 455830-1 (IS 7984)
Use Hand Tool No. 90123-5 for 1.09-1.90 [.043-.075] insulation diameter.

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)

i2 Technologies US, Inc.

HTML Pages converted to PDF Document

This document contains component information from the manufacturer's website which are not available in a revision controlled document from the manufacturer. To facilitate the addition of these parts into the Electronics Database, we are converting the HTML pages related to that part, from the manufacturer's website into Adobe PDF format. The contents of this document is based on the information provided on the manufacturer's website, therefore the information may have been changed by the manufacturer since this was created.

