

Distributed by:


JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1977809

796949-8 Product Details

 Product View

796949-8

 Part Status is Active

[Active](#)

Terminal Block Connectors

 [Always EU RoHS/ELV Compliant](#) [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- Housing Color = Black
- Not Stacked
- Without Threaded Flange
- Without Screw Flange

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [TERMINAL BLOCK PCB MOUNT W/INTERLOCK, 5.08mm PITCH](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- [Terminal Block Stacking Connectors](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Type Features:

- [Product Type](#) = Connector
- [Stacked](#) = No
- [Number of Positions](#) = 8
- [Connector Type](#) = Wire Receptacle
- [Mount Angle](#) = Vertical
- Screw Material = Brass

Mechanical Attachment:

- Screw Plating = Nickel

Electrical Characteristics:

- Voltage (VAC) = 250

Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 5.08 [0.200]
- [Wire Entry Diameter \(Solid Wire\) \(mm²\)](#) = 0.03 – 2.50
- [Wire Entry Diameter \(Stranded Wire\) \(mm²\)](#) = 0.03 – 1.50
- [Wire Entry Angle](#) = Side
- [Interlock](#) = With
- Wire Range (mm [AWG]) = 0.05-3.00 [30-12]
- Flammability Rating = UL 94V-0

Contact Related Features:

- [Threaded Flange](#) = Without
- [Screw Flange](#) = Without
- Contact Material = Brass
- Contact Mating Area Plating = Tin

Housing Related Features:

- [Housing Color](#) = Black
- Housing Material = Polyamide 6.6

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Buchanan

Languages: English | [Deutsch](#) | [Español](#) | [Português \(do Brasil\)](#) | [Русский](#) | [Italiano](#) | [\(\)](#) | [\(\)](#) | [\(\)](#)

Country Sites: [China](#) | [Japan](#)

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Supplier](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

© 2007 Tyco Electronics Corporation All Rights Reserved