



* NOTE: All relevant materials are complied with RoHS directive .

P1		P2
1		1
2		2
3		3
4		4
5		5
6		6
7		7
8		8
9		9
SHIELD		SHIELD

1006

5&6	BLACK HEAT SHRINK TUBE ϕ 3.0*22mm	2	M743
	ALUMINUM FOIL 33*65mm	2	M379
	MOLDED PE COLOR TRANSPARENT		TWN
	MOLDED PVC BLACK		M304
4	NON-UL 9C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 5.0mm, JACKET BLACK, DRAWING No. EMAL2809C-051	1810mm	M304
3	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BLACK	4	M95
2	DB9 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	1	M108
1	DB9 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	1	M108
No.	DESCRIPTION	Q'TY	Supplier
APPROVED		Cable Length	
CHECKED	TIAN	Unless Other Spec.	
DRAWING	PAFFY	Tolerances:	
DATE	28/JUN/07	0 ~200mm	±10mm
ITEM NO.	M692-05	201~1000mm	±20mm
		1001 ~1500mm	±25mm
		1501 ~2100mm	±30mm
		2100mm↑	±40mm

MSL
ENTERPRISES CORP.

CHECKED