

**MATERIALS**

- 1. CONTACT: BRASS
- 2. INSULATOR: PBT (UL 94V-0)
- 3. CONTACT PLATING: GOLD OVER NICKEL

**SPECIFICATION**



- 1. INSULATOR RESISTANCE: 5000M ohms Min
- 2. CURRENT RATING: 3 Amps
- 3. DIELECTRIC WITHSTANDING VOLTAGE: AC 500V
- 4. OPERATING TEMPERATURE: -45°C TO +105°C

Part Number :

2012-254-1xXX-RGA

XX : number of contacts

A : A type 16mm



TOP WILLING

TITLE	PIN HEADER PITCH=2.54mm Right Angle
DWG.NO.	P3-011XXX160RABG

SCALE	
SHEET	1 OF 1
UNIT	MM

APP.	LISA
CHK.	JACKY
DR.	DAVID

GENERAL TOLERANCE UNLESS SPECIFIED	
LINEAR	0.0±0.30
	0.00±0.20
ANGLES	±1°

REV