

Consolidated Electronic Wire & Cable

11044 King St

Franklin Park, IL 60131 US

Phone: 847-455-8830 Fax: 847-455-8837

Toll-free: 800-621-4278

Email: info@conwire.com Website: <http://www.conwire.com>

Part # 20 PE, 20 AWG Plain Enamel Magnet Wire (PE)



20 AWG Plain Enamel Magnet Wire (PE)

Product Construction

Construction 20 AWG (PE):

- Solid bare copper conductor
- Polyurethane / Polyamide (Nylon)
- (PE) Plain Enamel Magnet Wire
- Solderable:
 - 14-24 AWG at 430°C
 - 25-40 AWG at 360°C

Characteristics:

- Temperature: 14-24 AWG -30°C to +130°C
- MIL JW-1177/9, MW 28-C, Class 130
- Temperature: 25-40 AWG -30°C to +155°C
- MIL JW-1177/42, MW80-C, Class 155

Packing

- 1/4 lb. spools
- 1/2 lb. spools
- 1 lb. spools
- Also available on bulk spools

Sold in standard packages of five spools per gauge size and spool put-up.

SPECIFICATIONS

Conductor Size	20 AWG
Nominal O.D.	0.0334 in.
Spool Put-Up	1/4 lbs 1/2 lbs 1 lbs
Temperature	-30 to +130 °C