

Consolidated Electronic Wire & Cable

11044 King St


Franklin Park, IL 60131 US

Phone: 847-455-8830 Fax: 847-455-8837

Toll-free: 800-621-4278

Email: info@conwire.com Website: <http://www.conwire.com>

Part # 3819, 24 AWG Solid Bus Bar Wire, Tinned Copper Wire



24 AWG Solid Bus Bar Wire, Tinned Copper Wire

Product Construction

Conductor:

- Solid soft drawn Tinned Copper wire
- 24 AWG solid annealed tinned Copper wire

Insulation:

- None

Applications

- Bus bar point-to-point application
- Bell wire point-to-point connection

Industry Approvals

- ASTM B-33
- QQ-W-343, Type S
- MIL-W-3861, Type S

Packaging

- 1000 ft. spools
- 500 ft. spools
- 100 ft. spools
- Also available on bulk reels

[SPECIFICATIONS](#) · [OTHER INFORMATION](#) · [DISCLAIMER](#)

SPECIFICATIONS

Conductor Size	24 AWG
Strands	Solid
Conductor Material: Bare Copper or Tinned Copper	Tin Copper
Nominal O.D.	0.0200 in.
Circular Mil. Area	404.0
Ampacity	5 A

OTHER INFORMATION

Approvals	ASTM B-33 MIL-W-3861, Type S QQ-W-343, Type S RoHS
-----------	---

DISCLAIMER

Terms and Conditions for the Consolidated Electronic Wire and Cable Website Consolidated has made a very reasonable effort to ensure the accuracy of this "website" pertaining to the information, specifications and the "search" accuracy. The "website" is subject to errors and omissions. The content is subject to change without notice. This "website" is being constantly updated to correct any errors and omissions, but this does not ensure it is completely accurate. Drawings are for general reference only. Consolidated Electronic Wire & Cable is not liable for any direct, indirect, incidental or consequential damages resulting from the use of the material from this "website".
