

SPECIFICATION FOR APPROVAL

CUSTOMER: JAMES
PART NO: 2099121
MODEL NO: 5.5x2.1 AWG#18 6FT
DESIGNED NO: T0210 RoHS
REVISION: 1-1
CATEGORY: DC CORD
DATE SUBMITTED: 2014.11.21

SAMPLE/SPECIFICATION SUBMITTED		CONCLUSION	APPROVED
SAMPLE 0			REJECTED
SPECIFICATION 1			CONDITION APP'D

CUSTOMER'S SIGNATURE:

浩源實業有限公司
HAWK'S AIM INDUSTRIAL CO., LTD.
高雄市前鎮區新衙路 286-8 號 5F-2
5F-2, No.286-8, Shin-Ya Road, Chien-Chen
District, Kaohsiung, Taiwan 806
Tel:07-8418448 Fax:07-8419997

MODEL NO: 5.5x2.1 AWG#18 6FT
 CUSTOMER P/N: 2099121
 DESCRIPTION: DC CORD
 ISSUED DATE: 2014.11.21
 REVISION: 1-1

TABLE OF CONTENTS

1.0 APPEARANCE DIMENSION


REV	DESCRIPTION	DATE
1-0	INITIAL RELEASED	2009.09.22
1-1	CHANGE HAWK'S AIM	2014.11.21

APP.BY _____

CHK.BY _____

PRE.BY _____

1.0 APPEARANCE DIMENSIONS: (UNIT:mm)



BLACK WIRE —●— LETTERED WIRE

BLACK WIRE —●— LETTERED WIRE

- (1) MAXIMUM VOLTAGE RATING: 300V
- (2) MAXIMUM CURRENT RATING: 2.5Amp
- FUNCTION TEST: No open, no reversed polarity, no short-circuit, no INT
- CABLE ASSEMBLY SHALL BE IN COMPLIANCE WITH RoHS REQUIREMENT.
- HI-POT: 600VAC,0.5mA,1Second

APP.BY _____

CHK.BY _____

PRE.BY _____