




NOTES: 1) ALL WIRE LENGTHS ARE $\pm 1/2"$.
 2) ALL STRIP LENGTHS ARE $3/8" \pm 1/8"$.



INPUT: 113VAC TO 132VAC
 OUTPUT: 6.0KV TO 7.4KV @ 120VAC
 -AS MEASURED WITH HVPSI
 HV DIGITAL METER
 (<10G OHM IMPEDANCE)

CRITICAL MATERIALS:

- ENCAPSULANT - FILLED EPOXY, UL 94V0 RATED.
- PRIMARY WIRES - 22 GA, PVC, 600 V, UL STYLE 1015, 105°C.
- HV OUTPUT WIRE - 22GA, UL 3239, 15 KVDC.
- 21830 THERMFILM UL APPROVED LABEL