

DC Chip cooler

■ AP 35mm ~ 52mm
Thickness : min 08mm ~ max 12mm



45x45x10



40x40x08

*:Noise is measured at the distance of 1 meter from the axis of intake.
Specifications are subject to change without prior notice.

Bearing type: ●=Ball ※=Sleeve ●=Hypro Bearing

	Frame size (mm)	Model No.	Bearing Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (RPM)	Maximum AirFlow (CMM) (CFM)	Maximum Pressure (InAq) (mmAq)	*Noise Level (dB/A)	Weight (g)
AP3508	35x35x08	AP3505LX-J70(TX)	●	5	0.07	0.35	7500	0.07 2.40	0.08 2.05	20.0	12
	35x35x08	AP3505MX-J70(TX)	●	5	0.11	0.55	9000	0.09 3.30	0.14 3.45	27.9	12
	35x35x08	AP3505HX-J70(TX)	●	5	0.13	0.65	10500	0.12 4.10	0.15 3.78	32.0	12
	35x35x08	AP3512MX-J70(TX)	●	12	0.10	0.72	9000	0.09 3.30	0.14 3.45	27.9	12
	35x35x08	AP3512HX-J70(TX)	●	12	0.11	1.08	10500	0.12 4.10	0.15 3.78	32.0	12
AP4008	40x40x08	AP0405MX-J70	●	5	0.10	0.50	7000	0.13 4.70	0.11 2.78	28.0	15
	40x40x08	AP0412MX-J70	●	12	0.06	0.72	7000	0.13 4.70	0.11 2.78	28.0	15
AP4010	40x40x10	AP0405MX-G70	●	5	0.13	0.65	8000	0.13 4.70	0.11 2.78	28.0	20
	40x40x10	AP0412LX-G70	●	12	0.05	0.60	6500	0.10 3.50	0.06 1.58	19.0	20
	40x40x10	AP0412MX-G70	●	12	0.07	0.84	8000	0.13 4.70	0.11 2.78	28.0	20
AP4508	45x45x08	AP4505LX-J90	●	5	0.04	0.20	4500	0.12 4.20	0.04 1.12	19.5	20
	45x45x08	AP4505MX-J90	●	5	0.07	0.35	5500	0.15 5.20	0.06 1.63	23.8	20
	45x45x08	AP4505HX-J90	●	5	0.09	0.45	6200	0.17 6.00	0.09 2.29	30.0	20
	45x45x08	AP4512LX-J90	●	12	0.04	0.48	4500	0.12 4.20	0.04 1.12	19.5	20
	45x45x08	AP4512MX-J90	●	12	0.05	0.60	5500	0.15 5.20	0.06 1.63	23.8	20
	45x45x08	AP4512HX-J90	●	12	0.05	0.60	6200	0.17 6.00	0.09 2.29	30.0	20
AP4510	45x45x10	AP4505LX-G90	●	5	0.05	0.25	4800	0.13 4.50	0.05 1.30	19.9	20
	45x45x10	AP4505MX-G90	●	5	0.08	0.40	5800	0.16 5.50	0.07 1.70	25.0	20
	45x45x10	AP4505HX-G90	●	5	0.09	0.45	6500	0.17 6.00	0.09 2.29	30.0	20
	45x45x10	AP4512LX-G90	●	12	0.04	0.48	4800	0.13 4.50	0.05 1.30	19.9	20
	45x45x10	AP4512MX-G90	●	12	0.05	0.60	5800	0.16 5.50	0.07 1.70	25.0	20
	45x45x10	AP4512HX-G90	●	12	0.05	0.60	6500	0.17 6.00	0.09 2.29	30.0	20
AP5008	50x50x08	AP0505LX-J90	●	5	0.05	0.25	4300	0.18 6.20	0.06 1.40	23.0	24
	50x50x08	AP0505MX-J90	●	5	0.08	0.40	5000	0.20 7.10	0.07 1.85	25.5	24
	50x50x08	AP0505HX-J90	●	5	0.08	0.40	6300	0.26 9.20	0.10 2.58	32.6	24
	50x50x08	AP0512LX-J90	●	12	0.05	0.60	4300	0.18 6.20	0.06 1.40	23.0	24
	50x50x08	AP0512MX-J90	●	12	0.05	0.60	5000	0.20 7.10	0.07 1.85	25.5	24
	50x50x08	AP0512HX-J90	●	12	0.08	0.96	6300	0.26 9.20	0.10 2.58	32.6	24
AP5212	52x52x12	AP5212MX-E70(8)	◎ ●	12	0.06	0.72	4300	0.30 9.30	0.07 2.50	20.8	25
	52x52x12	AP5212HX-E70(8)	◎ ●	12	0.08	0.96	5200	0.33 11.80	0.13 3.30	27.0	25