



SPECIFICATIONS SHEET

PRODUCT TYPE : PIEZO BUZZER

PRODUCT SERIES : DB-E78

DESCRIPTION : PZ BUZZER PULSE 12VDC L/W ABS

RoHS

COLOR : BLACK

ELECTRICAL SPECIFICATIONS

MODEL NO.	7P3120LFLA
OPERATING VOLTAGE RANGE (VDC)	3 ~ 15
RATED VOLTAGE (VDC)	12
* MAX. RATED CURRENT (mA)	10
* MIN. SOUND OUTPUT (dBA/ 30 cm)	90
* FREQUENCY (Hz)	3200 ± 500
TONE NATURE	PULSE
OPERATING TEMPERATURE (°C)	- 20 ~ +60
TERMINAL	LEADWIRE
HOUSING MATERIAL	ABS
WEIGHT (g)	15

* Value applying at rated voltage

DIMENSIONS

UNIT : mm

