

**ADDA USA  
AC FAN SPECIFICATIONS**

Frame Size	Model Part No.	Bearing Type	Input Volt. / Freq (V/Hz)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (mmAq)	Noise (dB/A)	Weight (g)	Connection Type	Safety Approvals	Units Per Box	Box Wt (LBS.)
80 X 80 X 25	AA8251MB-AT(AW)	B,S,or X	115/50	0.15	17.3	1900	14.6	1.5	18.3	191	Terminal or Lead Wires	CE	200	91
			115/60	0.13	14.9	2500	18.9	2.75	24					
80 X 80 X 25	AA8252MX-AT(AW)	B,S,or X	230/50	0.07	16.1	1850	14.6	1.5	18.3	191	Terminal or Lead Wires	CE	200	91
			230/60	0.06	13.8	2450	18.9	2.75	24					
80 X 80 X 38	AA8381HS-AT(AW)	B,S,or X	115/50	0.13	8.98	2300	24	2.73	25.3	309	Terminal or Lead Wires	UL,CUL,TUV,CE	60	55
			115/60	0.1	6.75	2800	29.6	4.17	31.6					
80 X 80 X 38	AA8381MS-AT(AW)	B,S,or X	115/50	0.08	5.42	2300	24	2.73	25.3	309	Terminal or Lead Wires	UL,CUL,TUV,CE	60	55
			115/60	0.07	4.61	2400	25.1	3.04	26.2					
80 X 80 X 38	AA8382HS-AT(AW)	B,S,or X	230/50	0.07	8.8	2300	24	2.73	25.3	309	Terminal or Lead Wires	UL,CUL,TUV,CE	60	55
			230/60	0.06	6.8	2800	29.6	4.17	31.6					
80 X 80 X 38	AA8382MS-AT(AW)	B,S,or X	230/50	0.05	6.8	2300	24	2.73	25.3	309	Terminal or Lead Wires	UL,CUL,TUV,CE	60	55
			230/60	0.05	5.7	2400	25.1	3.04	25.3					
92 X 92 X 25	AA9251MS-AT(AW)	B,S,or X	115/50	0.15	17.3	1650	22.8	1.15	21.1	220	Terminal or Lead Wires	CE	200	55
			115/60	0.13	14.9	2150	29.1	1.83	26.8					
92 X 92 X 25	AA9252MB-AT(AW)	B,S,or X	230/50	0.07	16.1	1650	22.8	1.15	21.1	220	Terminal or Lead Wires	CE	200	55
			230/60	0.06	13.8	2150	29.1	1.83	26.8					
120 X 120 X 25	AA1251MS-AT(AW)	B,S,or X	115/50	0.22	23	2050	61	3.23	38.7	339	Terminal or Lead Wires	UL,CUL,CE	90	75
			115/60	0.19	19.6	2400	69.4	3.85	44.1					
120 X 120 X 25	AA1252MS-AT(AW)	B,S,or X	230/50	0.11	20.7	2050	61	3.23	38.7	339	Terminal or Lead Wires	UL,CUL,CE	90	75
			230/60	0.1	18.4	2400	69.4	3.85	44.1					
120 X 120 X 38	AA1281UX-AW(AW)	B,S,or X	115/50	0.33	25.82	2500	100.2	0.24	45.8	545	Terminal or Lead Wires	CE	40	55
			115/60	0.27	21.43	2800	110	0.21	48.3					
120 X 120 X 38	AA1281HB-AT(AW)	B,S,or X	115/50	0.25	16.3	2400	92.6	4.8	43.5	545	Terminal or Lead Wires	CE	40	55
			115/60	0.2	14.2	2500	100.2	4.55	44.9					
120 X 120 X 38	AA1282UX-AT(AW)	B,S,or X	230/50	0.17	25.61	2500	100.2	0.24	45.8	545	Terminal or Lead Wires	CE	40	55
			230/60	0.13	20.96	2800	110	0.21	48.3					
120 X 120 X 38	AA1282HB-AT(AW)	B,S,or X	230/50	0.12	16	2400	92.6	4.8	43.5	545	Terminal or Lead Wires	CE	40	55
			230/60	0.1	14	2500	100.2	4.55	44.9					
120 X 120 X 38	AA1281HX-AT(AW)	B,S,or X	115/50	0.25	16.28	2600	83	0.28	42.2	547	Terminal or Lead Wires	UL,CUL,TUV,CE	40	55
			115/60	0.2	14.21	2900	93	0.25	44.5					
120 X 120 X 38	AA1281MX-AT(AW)	B,S,or X	115/50	0.25	15.76	2500	81.5	0.24	40	547	Terminal or Lead Wires	UL,CUL,TUV,CE	40	55
			115/60	0.21	13.74	2700	86.4	0.15	41					
120 X 120 X 38	AA1281LX-AT(AW)	B,S,or X	115/50	0.14	9.21	2400	75.9	0.17	40.1	547	Terminal or Lead Wires	UL,CUL,TUV,CE	40	55
			115/60	0.13	8.86	2100	63.8	0.08	37.9					
120 X 120 X 38	AA1281DX-AT(AW)	B,S,or X	115/50	0.12	8.24	2300	73.5	0.14	39.2	547	Terminal or Lead Wires	UL,CUL,TUV,CE	40	55
			115/60	0.11	7.89	1650	51.4	0.06	30.5					
120 X 120 X 38	AA1282HX-AT(AW)	B,S,or X	230/50	0.12	16	2600	83	0.28	42.2	547	Terminal or Lead Wires	UL,CUL,TUV,CE	40	55
			230/60	0.1	14	2900	93	0.25	44.5					
120 X 120 X 38	AA1282MX-AT(AW)	B,S,or X	230/50	0.1	13.7	2500	81.5	0.24	40	547	Terminal or Lead Wires	UL,CUL,TUV,CE	40	55
			230/60	0.09	12.6	2700	86.4	0.15	41					
120 X 120 X 38	AA1282LX-AT(AW)	B,S,or X	230/50	0.07	9.9	2400	75.9	0.17	40.1	547	Terminal or Lead Wires	UL,CUL,TUV,CE	40	55
			230/60	0.07	9.4	2100	63.8	0.08	37.9					
120 X 120 X 38	AA1282DX-AT(AW)	B,S,or X	230/50	0.06	8	2300	73.5	0.14	39.2	547	Terminal or Lead Wires	UL,CUL,TUV,CE	40	55
			230/60	0.06	7.6	1650	51.4	0.06	30.5					
172 X 150 X 50	AA1751HB-AT(AW)	B,S,or X	115/50	0.48	59.6	2700	194.6	12.75	52.3	922	Terminal or Lead Wires	UL,CUL,CE	20	47.3
			115/60	0.43	39.3	3000	218.2	7.75	54.7					
172 X 150 X 50	AA1751MB-AT(AW)	B,S,or X	115/50	0.35	29.8	2600	186	9.25	50.5	922	Terminal or Lead Wires	UL,CUL,CE	20	47.3
			115/60	0.34	29.3	2500	177.4	3.5	48.8					
172 X 150 X 50	AA1752HB-AT(AW)	B,S,or X	230/50	0.27	47.9	2700	196	12.25	51.3	922	Terminal or Lead Wires	UL,CUL,CE	20	47.3
			230/60	0.23	38.4	3000	217.7	7.25	53.9					
172 X 150 X 50	AA1752MB-AT(AW)	B,S,or X	230/50	0.19	32.6	2600	185.3	9	50.4	922	Terminal or Lead Wires	UL,CUL,CE	20	47.3
			230/60	0.19	29.9	2500	178.6	3.25	48.9					

NOTE B=Ball S=Sleeve X= Hypro AT= Terminals AW= Wires

**ADDA USA ALL RIGHTS RESERVED**

**All specifications subject to change without notice.**