



ASUS DE07015R12U 3-Pin Fan

- ASUS DE07015R12U
- Dimensions: 70x70x15 MM
- Voltage: DC 12V
- Operating Voltage: DC 5V ~ 13.2V
- Current: 0.7A
- Speed: 5700 RPM
- Air Flow: 43 CFM
- Air Pressure: 0.31 Inch-H2O
- Bearing: Hydraulic
- Termination: 3-Pin / 3-Wire