

Specifications

Features:

- *Regular barrier construction
- *Mounting ends available
- *UL and CSA recognized
- *5 pin styles to choose from
- *Accepts #12 AWG

Electrical

Current:	20A @ 300V
Wire range:	12 to 22 AWG
Withstanding voltage:	2000V AC per min.
IR:	>1000M Ω (500V DC)
Operating temp:	-40° C to +105° C
Torque:	12 lb-in

Materials

Housing:	Polyamide 6,6 (UL94V-0)
Terminal:	Brass, Tin plated
Screw:	M3 combo head w/captive sems plate

20A 300V

8.25mm (.325")

