



DeoxIT® SHIELD SN5 Spray

Contact Cleaner, Enhancer & Protector

Part No.: SN5S-6N
Formulation: 5% DeoxIT® SHIELD S100L (formerly PreservIT)
 70-74% 1,1,1,3,3-PENTAFLUOROPROPANE (460-73-1)
 1-5% isopropyl alcohol (67-63-1)
 20% hydrocarbon propellant (75-28-5, 74-98-6)
Container Size: 163 g



Product Description:

Contact lubricant and protectant for metal surfaces. Oxidation and corrosion deterrent. Improves conductivity, maintains optimum signal quality. DeoxIT® SHIELD also reduces wear and abrasion, arcing, RFI and intermittent connections and improves connector performance/reliability. Ideal for severe environments. On oxidized surfaces, pre-treat with DeoxIT® contact cleaner. Temperature range: -34 to +210°C.

Features/Benefits:

100% Liquid - Safe on Plastics.

DeoxIT® SHIELD S100L concentrate has 0.0% chemical cleaning action. Ideal for severe environments (humidity, salts, pollutants, sulfur, etc.) Excellent protection, good conductivity enhancing, excellent lubrication. Creates a long lasting barrier against oxidation and corrosion. No ozone depletion. Reduces intermittent connections, arcing, RFI, wear and abrasion.

Cleaner Audio - Clearer Video - Reliable Data.

Other Applicators:

S5S-6	5%	spray	142 g	flammable
S5MS-15	5%	mini-spray	14 g	flammable
SN5MS-15	5%	spray	14 g	nonflammable
S100S-2	100%	spray	57g	nonflammable
S100P	100%	pen	6 mL	nonflammable
S50W	100%	wipes	50 count	nonflammable
S100L-2DB	100%	brush	7.4 mL	nonflammable
S100L-25C	100%	needle dispenser	25 mL	nonflammable
S100L (bulk)	100%	bottle/drum	assort.	nonflammable
S5L (bulk)	5%	bottle/drum	assort.	flammable

DeoxIT® Essential Reference:

DeoxIT® - Brings old systems back to life!

DeoxIT® GOLD - Maintains new system performance!

DeoxIT® SHIELD - Maintains new system performance for severe environments!

Shipping Information:

Hazardous: Y - ORMD

Other Information:

RoHS Compliant: YES

SN5S-6N MSDS Link:

<http://store.caig.com/app/site/media/sitemedia.nl/id.1554/.f>

DeoxIT® shield Product Sheet:

<http://store.caig.com/app/site/media/sitemedia.nl/id.989/.f>

MentorCard Link:

http://www.caig.com/pdf/MentorCards_2006_av.pdf

MANUFACTURER DISCLAIMER:

To the best of our knowledge, the information contained herein is accurate. However, neither CAIG Laboratories, Inc., or any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. All materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist. All service performed on internal parts and equipment should be provided by qualified technicians.

Contact Information:



North America

CAIG Laboratories, Inc.
12200 Thatcher Court
Poway, CA 92064 USA
Tel: (858) 486-8388
Fax: (858) 486-8398

Website

www.caig.com

General email

caig123@caig.com

Technical email

tech@caig.com