

SAT METER

S F - 0 2



■ FEATURE

- **SMALL AND SMART DESIGNED** satellite SIGNAL STRENGTH METER
- **ANALOG METER** for easier readouts
- **Buzzer** for **ACOUSTIC** signal strength monitoring
- **Frequency range** 950MHz to 2,050MHz
- **Highest input sensitivity** through MMIC technology
- **Built in integrator** for **BROAD BAND FREQUENCY** scanning
- **LED indicator** for horizontal (18V) or vertical (13V) polarization

■ Technical Specification

- Frequency range: 950 MHz to 2,050 Mhz
- Detection Range: -40 to -10 dBm
- Input impedance: 75 Ω
- Insertion Losses: 4 dB approx.
- Indication: Analog Panel Meter
- Acoustic Indicator: 2 kHz to 20 kHz
- Connector: "F" Female type
- Dimension: 95(W) x 55(D) x 30(H) mm
- Weight: Approx. 120 g

■ Packing Details

- Individual Packing: Blister Pack
- Inner Carton: Q'TY/CTN: 20PCS,
SIZE: 340(W)x195(D)x26(H)mm
G.W.: 2.2 kg
- Out Carton: Q'TY/CTN: 60PCS
Size: 310(W)x510(D)x350(H)mm
G.W.: 9 kg, N.W.: 7.5 kg