

## Servo specification

### Item No.: RS001A

Weight:	8g
Size:	23 x 12.3 x 25.6 mm
Torque:	1.5 kg/cm(at 4.8V)
Speed:	0.12sec/60°(at 4.8V)
Gear Type:	Plastic
Motor Type:	Coreless
Operating Voltage Range:	4.8v-6v
Operating Temperature Range:	0°C -60°C
Current:	< 500mA
Dead Bend Width:	4 usec
Connector Wire Length:	170mm

