

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.

NO	TEST ITEM	TEST CONDITION / SPECIFICATION	RESULT	VERDICT							
9	SET UP TIME	I/P:12VDC O/P:FULL LOAD SPEC: NONE	A:9.8mS	P							
10	EFFICIENCY	I/P: 12VDC O/P:FULL LOAD SPEC: 73%	A:73.0% B:78.7% C:81.2%	P							
11	INSULATION RESISTANCE	SPEC:I/P-O/P 500VDC/1000M Ohms MIN.	A:I/P-O/P >100M Ohms	P							
12	DIELECTRIC / WITHSTAND VOLTAGE	SPEC: I/P- O/P: 1000VDC/ 1 min (10mA CUT-OFF)	A:NO BREAK I/P-O/P: :<0.02mA	P							
13	BURN-IN TEST	I/P:12VDC TA:25 °C O/P:FULL LOAD BURN-IN DURATION : 2 hrs	A:NO BREAK B:NO BREAK C:NO BREAK	P							
14	TEMPERATURE RISE TEST T rise OF PARTS	A:I/P :12VDC O/P :FULL LOAD TA:25 °C AFTER 4 hrs BURN-IN <table border="1" data-bbox="592 689 1193 752"> <thead> <tr> <th>POSITION</th> <th>SAMPLE</th> <th>TEMP</th> <th>T rise</th> </tr> </thead> <tbody> <tr> <td>CASE</td> <td>DLW05A-05</td> <td>42.7°C</td> <td>17.7°C</td> </tr> </tbody> </table>	POSITION	SAMPLE	TEMP	T rise	CASE	DLW05A-05	42.7°C	17.7°C	P
POSITION	SAMPLE	TEMP	T rise								
CASE	DLW05A-05	42.7°C	17.7°C								
15	CONSTRUCTION INSPECTION (FOR QC INSPECTION REFERENCE ONLY)	A: 1. PACKING : 上下夾泡棉外加紙盒包裝 2. MARKING : MODEL 3. MECHANICAL: SIX-SIDED SHIELD METAL CASE 4. DIMENSIONS : WXHXD=50.8X11.27X25.4mm, PIN : 1.0Øx8.3mm									
DATE	SAMPLE	TEST RESULT	TEST	APPROVAL							
1998.12.04	DLW05A-05 DLW05A-12 DLW05A-15	PASS	T.K.CHENG	MAX LIN							

[PREVIOUS](#)