

## Switching Power Supply

**PS-1203 / 1820 / 2415 / 3610 / 6006**



### ■ FEATURE

- A wide AC input voltage 108V – 132V (for 120V ) and 196V-264V (for 230V).
- High frequency operation reduces the size of power transformer.
- Small size, light weight and high power in small area.
- Efficiency is greater than 72%.
- Automatic control for voltage and constant current modes
- Zero adjustment for the output of voltage and current.

### ■ TECHNICAL SPECIFICATIONS

**Main Supply : 120V±10% 50/60Hz or 230V ±15% (factory set)**

MODEL	MAX. RATING		Weight	Dimension(mm)
	Voltage	Current		
MODEL			Weight	Dimension(mm)
<b>PS1230</b>	12V	30A	3.88kg	310 x 138 x 155
<b>PS1820</b>	18V	20A	3.85kg	310 x 138 x 155
<b>PS2415</b>	24V	15A	3.85kg	310 x 138 x 155
<b>PS3610</b>	36V	10A	3.85kg	310 x 138 x 155
<b>PS6006</b>	60V	6A	3.8kg	310 x 138 x 155

Input Rating : 500 Watts / 900 VA

Fuse Style & Rating: : 120V -- T10A 250V

230V -- T6.3A 250V

**WARNING:** Voltage over 60V DC is a lethal shock hazard to the user.

Be careful when connecting power supplies in series to achieve voltages higher than 60V DC or 60V DC between any connection terminal and earth ground.

Operation Environment : Indoor use

Altitude up to 2000m

Operation Temperature & Humidity: 0° C to 40° C (32° F to 104 ° F) @ 80%

Storage Temperature & Humidity: -10° C to 70°C (14° F to 158° F) @ 70%

Standard Accessory: Instruction Manual, Test Leads, Spare Fuse

#### HEAD OFFICE

201 Century Business Center,  
 1337-20 Daeryung Seocho Tower Bldg B1, Seocho-2 Dong, Seocho-Gu,  
 Seoul 137-751, Korea  
 Phone : (82-2) 553-4766 , Fax : (82-2) 553-4764

#### USA OFFICE

10585 Bloomfield Street  
 Alamitos Business Center  
 Los Alamitos, CA 90720, USA  
 Phone # : (562) 493-7959

**Constant Voltage Operation**

No	ITEM	PS1230	PS1820	PS2415	PS3610	PS6006
1	Voltage Output	0~12V	0~18V	0~24V	0~36V	0~60V
2	Line Regulation	≤5mV	≤5mV	≤5mV	≤5mV	≤5mV
3	Load Regulation	≤5mV	≤5mV	≤5mV	≤5mV	≤5mV
4	Ripple	≤5mVrms	≤5mVrms	≤5mVrms	≤5mVrms	≤5mVrms
5	Ripple & Noise	≤100mVp-p	≤100mVp-p	≤100mVp-p	≤100mVp-p	≤100mVp-p

**Constant Current Operation**

No	ITEM	PS1230	PS1820	PS2415	PS3610	PS6006
1	Current Output	30A Max	20A Max	15A Max	10A max	6A max
2	Line Regulation	≤3mA	≤3mA	≤3mA	≤3mA	≤3mA
3	Load Regulation	≤3mA	≤3mA	≤3mA	≤3mA	≤3mA
4	Ripple & Noise	≤5mArms	≤5mArms	≤5mArms	≤5mArms	≤5mArms

**HEAD OFFICE**

201 Century Business Center,  
 1337-20 Daeryung Seocho Tower Bldg B1, Seocho-2 Dong, Seocho-Gu,  
 Seoul 137-751, Korea  
 Phone : (82-2) 553-4766 , Fax : (82-2) 553-4764

**USA OFFICE**

10585 Bloomfield Street  
 Alamitos Business Center  
 Los Alamitos, CA 90720, USA  
 Phone # : (562) 493-7959