



Mallory Sonalert Products, Inc.

Part #:

SCM616N-1

Sales Outline Drawing

Revision:

A

Specifications:

Sound Level Category	Extra Loud
Mode of Operation	Continuous
Voltage Rating	6 to 16 Vdc
Frequency	2900 ± 500 Hz
Loudness @ 2 FT	95 to 105 dB(A) Typ.
Loudness @ Min Vdc	80 dB (A) @ 2 ft. and 6 Vdc
Loudness @ Max Vdc	95 dB (A) @ 2 ft. and 16 Vdc
Current Draw	30mA MAX
Housing Material	6/6 Nylon, Color: Black
Storage Temperature	-40° to +85° C
Operating Temperature	-40° to +85° C
Mounting	PC Pins- Mount on Circuit Board
Weight (Typical)	1.6 oz (45g)
Options	Please contact factory.

Dimensions: Inches (mm)

