


Specifications

- Current & Voltage Rating : 3A & 25Vac max.
- Insulation Resistance : 5000 MΩ min.
- Contact Resistance : 20 mΩ max.
- Dielectric Withstanding : AC 500V
- Operating Temperature : -25°C ~ +85°C
- Contact Material : Phosphor Bronze
- Insulator Material : PBT UL 94V-0 (Black)
- Finish : Gold plated
- Packing : Tray



Recommended P.C.B. Layout

						TOLERANCES UNLESS OTHERWISE SPECIFIED		TOP WILLING CO., LTD.				
						X. ±0.30	X.°					Customers
						.X	X.X°	Drawing	Straight Type L:14.7mm			
						.XX		Part NO.	PCB1xxS-D14.7	Scale	1 : 1	
						.XXX		Old Part No.		Sheet	1 of 1	
	R1	2015/10/29	NEW	Maggie	CHKD	APVD	APVD	UNIT	mm	SIZE	A4	 Third Angle Projection
ECN(DCN) NO.	REV.	DATE	DESCRIPTION	CHANGE	APVD	APVD						