


Date	Rev.	Description

### SPECIFICATION

Item No. 2177694  
 Product: Solder Wire Series



Composition (%)	Wire Diameter (mm)	Weight (g)	Package
Sn (tin) 60%, Pb (lead) 40%	0.3 ± 0.05	500	Roll
Sn (tin) 60%, Pb (lead) 40%	0.4 ± 0.05	500	Roll
Sn (tin) 60%, Pb (lead) 40%	0.5 ± 0.05	500	Roll
Sn (tin) 60%, Pb (lead) 40%	0.6 ± 0.05	500	Roll
Sn (tin) 60%, Pb (lead) 40%	0.8 ± 0.1	500	Roll
Sn (tin) 60%, Pb (lead) 40%	1.0 ± 0.1	500	Roll
Sn (tin) 60%, Pb (lead) 40%	1.2 ± 0.1	500	Roll
Sn (tin) 60%, Pb (lead) 40%	1.4 ± 0.1	500	Roll
Sn (tin) 60%, Pb (lead) 40%	1.6 ± 0.1	500	Roll


MATERIAL:		<b>GOLDSUN ELECTRONICS CO., LTD.</b>			
		JAMECO NO. <b>2177694</b>		GOLDSUN NO. <b>GSR-123</b>	
DRAWN: nomo		Description <b>1-Pound 0.015" Diameter Solder Roll</b>			Rev. 1
VERIFY PEOPLE: Chesley		UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No:

DCC. NO.
A4 DRAWING NO.

Date	Rev.	Description

**SPECIFICATION**

Item No. **2177694**  
 Product: **Solder Wire Series**



Composition (%)	Wire Diameter (mm)	Weight (g)	Package
Sn (tin) 60%, Pb (lead) 40%	0.3 ± 0.05	500	Roll
Sn (tin) 60%, Pb (lead) 40%	0.4 ± 0.05	500	Roll
Sn (tin) 60%, Pb (lead) 40%	0.5 ± 0.05	500	Roll
Sn (tin) 60%, Pb (lead) 40%	0.6 ± 0.05	500	Roll
Sn (tin) 60%, Pb (lead) 40%	0.8 ± 0.1	500	Roll
Sn (tin) 60%, Pb (lead) 40%	1.0 ± 0.1	500	Roll
Sn (tin) 60%, Pb (lead) 40%	1.2 ± 0.1	500	Roll
Sn (tin) 60%, Pb (lead) 40%	1.4 ± 0.1	500	Roll
Sn (tin) 60%, Pb (lead) 40%	1.6 ± 0.1	500	Roll

DCC. NO.  
 A4 DRAWING NO.

MATERIAL:		<b>GOLDSUN ELECTRONICS CO., LTD.</b>	
		JAMECO NO. <b>2177694</b>	GOLDSUN NO. <b>GSR-123</b>
DRAWN: nomo		Description <b>1-Pound 0.015" Diameter Solder Roll</b>	
VERIFY PEOPLE: Chesley		UNIT: mm	SCALE: SHEET 1 OF 1
		CAS No: ERN No:	Rev. <b>1</b>