





Date	Rev.	Description

	PARTS NAME	THE PARTS OF MATERIAL	ELECTROPLATING	RoHS No
1	Slide Handle	Brass	Plate Chromium	RoHS
2	Spring	Steel wire	-----	RoHS
3	Bushing	Brass	Plate Nickel	RoHS
4	Supporting Halt	Brass	-----	RoHS
5	Sliding Point	Bakelite	-----	RoHS
6	Housing	Bakelite	-----	RoHS
7	Movable Plate	Brass	Plate Silver	RoHS
8	Terminals	Brass	Plate Silver	RoHS
9	Nuts	Brass	Plate Nickel	RoHS
10	Zigzag Washer	Stainless Steel	-----	RoHS
11	Fix Washer	Stainless Steel	-----	RoHS
12	Steel crust	Stainless Steel	-----	RoHS
13	Epoxy Seal		-----	RoHS



Circuit Diagram

Specification

Rating: 2A 250V AC ;5A 125V AC
 Contact R: 20 mΩ Max
 Insulation R: DC500V 1000MΩ Min
 Dielectric strength: 1500V AC,1minute
 Electrical life:10,000 Cycles

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.	
DRAWN: Ivan Wang		JAMECO NO. 21952-100	GOLDSUN NO. GS-20311
VERIFY PEOPLE: Jenny		Description MINI TOGGLE SWITCH DPDT ON-OFF-ON 6P SOLDER LUGS	
UNIT: mm	SCALE:	SHEET 1 OF 1	Rev. 1 CAS No: ERN No:

DCC. NO.
A4 DRAWING NO.