

# 12VDC ~ 24AMP REGULATED POWER SUPPLY

PS24B is a high powered, 12VDC ~ 24 Amp Desktop Power Supply.

Perfect for Hobbyists: Model Railroads, slot car racing, science projects and other applications requiring 12VDC Regulated Power.

Features Standard 12VDC Cigarette lighter outlet and 6' power cord with 2.1mm right angle plug.

Includes US IEC Power cord. 100 ~ 240VAC auto sensing power supply allows this unit to be used anywhere in the world.  
*(World Power Cords not included)*



Model: PS24B



## SPECIFICATIONS:

- Input: 100 - 240V 50/60Hz World Product
- Max Output: 12VDC ~ 24 Amps
- cULus Recognized Power Supply
- UL / CUL / CCC / TUV Approved Power Supply
- Includes 6' IEC Power Cord (US/UL Style)
- Includes 6' 12VDC Cigarette Lighter Power Cord with 2.1mm right angle plug
- Heavy Duty Binding Posts
- Dimensions: 14½" x 6" x 3½"
- Includes Multi-Lingual Instruction Sheet
- Individually Boxed / 6 per carton
- Net Weight: 9 lb
- Black Color



Cigarette Lighter Cord Included