



REV	ZONE	REVISION	DATE

NO.	NAME	MATERIAL	FINISH	Q'TY
1	BARREL	C.R.S T:0.3	TIN-PLATED	1
2	TERMINAL	BRASS T:0.25	TIN-PLATED	1
3	BRACKET	C.R.S T:0.4	TIN-PLATED	1
4	INSULATOR	PBT G.F.	WHITE	1
5	RING	PBT G.F.	YELLOW/WHITE/RED/BLACK/BLUE	1

Specification:

Contact Resistance: 30m Ohm. Max. At AC 100mA Max. 1KHz.
 Insulation Resistance: 100M Ohm Min. At 500V DC.
 Rated Voltage And Current: DC 12V, 2A Max ; AC 100V, 1A Max.
 Dielectric Withstanding Voltage: 500VAC At 60Hz For 1 Minute.
 Durability (Life Test): 4000 Cycles.
 Insertion Force: 0.3~3.0 Kg.
 Extraction Force: 0.3~3.0 Kg.



TOP WILLING CO., LTD.

COMPUTER NO.			UNIT	SCALE	PART NAME	
D:\DWG\KY-006-1			mm	1:1	RCA JACK	
APPD.	CKD.	DWG.	DATE	TOLERANCE	PART NO.	REV.
		TINA	08-01-08	X. ± 0.38 X. ± 0.25 XX ± 0.13 XXX ± 0.05		A

MODEL KY-006-1 PAGE 1 OF 1