


Date	Rev.	Description





伍、(材料分析表) MATERIAL LIST :

NO	材料	材質	安規驗證
1	BOBBIN	NYLON	E41938 (M)
2	SILICON	H 50	N/A
			N/A
			N/A
3	WIRE	2UEW 130°C	E84201
			E :
			E :
4	TAPE		E17385
5	PAPER	0.25 mm	E :
6	銅釘	2P	
7	銅釘	3P	
8	L 腳		

MATERIAL	GOLDSUN ELECTRONICS CO., LTD.		
	JAMECO NO. 221365	GOLDSUN NO. EI86-40 117V	
DRAWN: Colin	Description POWER TRANSFORMER,24VCT@4A, 117VAC,LUGS		Rev. 1
VERIFY PEOPLE: Annie	UNIT: mm	SCALE:	SHEET 1 OF 1
			CAS No: ERN No:

DCC. NO.
A4 DRAWING NO.


Date	Rev.	Description



DCC. NO.
A4 DRAWING NO.

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
DRAWN: Colin		JAMECO NO. 221365	GOLDSUN NO. EI86-40 117V		
VERIFY PEOPLE: Annie		Description POWER TRANSFORMER,24VCT@4A, 117VAC,LUGS		Rev.	1
UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No:		

Date	Rev.	Description



1.Type	Single Phase Transformer	10.Temperature Rise	Under 70deg Resisting Method
2.Output Capacity	96 VA	11.Voltage Variation	Under 10%
3.Primary Rating Voltage	117V	12.Voltage Deviation	Under ±5%
4.Secondary Rating Voltage	P1 : 12V P2 : 24V	13.Environment	RoHS
5.Secondary Rating Current	P1 : 4A P2 : 4A		
6.Frequency	50/60Hz		
7.Time Rating	Continuous		
8.Isolation Resistance	Above DC500V 100MΩ		
9.Isolation Strength	AC1500V 50Hz P-S in 1 minute		

DCC. NO.
A4 DRAWING NO.

MATERIAL	GOLDSUN ELECTRONICS CO., LTD.		
	JAMECO NO. 221365	GOLDSUN NO. EI86-40 117V	
DRAWN: Colin	Description POWER TRANSFORMER,24VCT@4A, 117VAC,LUGS		Rev. 1
VERIFY PEOPLE: Annie	UNIT: mm	SCALE:	SHEET 1 OF 1
			CAS No: ERN No: