



Body Material: PP
 Wire Gauge: 1007 #20AWG
 Temperature rating : 80 °C
 Rated voltage : 300 v

				Item#	2221448	Part#	BF-301-T-B20#	Rev.	0
Modify	Date	Revision		Approval No.	Title	In-Line Fuse Holder		Unit	m/m
					Mat'l	Finish		Ratio	1.5:1
Size	0.5-6	>6-30	>30-120	>120-400	Auth	林協德	CHK	Derek DWG	Ring
Tol	+/-0.05	+/-0.1	+/-0.15	+/-0.2				Date	2017.08.22
								Proj.	3rd