

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242


The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 222608

P1: M-942A

P2: M-945A

Customer No:



9461-16			
P1		P2	
1	—————	1	RED 24#
2	⌵⌶	2	WHITE
3	⌵⌶	3	GREEN
4	—————	4	BLACK 24#
SHIELD	—————	SHIELD+BRAID	

* NOTE: All relevant materials are complied with RoHS directive .

5	MOLDED PVC BEIGE		M304
4	MOLDED PVC BEIGE		M304
3	USB 2.0 CABLE, UL STYLE 1 TWISTED PAIR 28AWG AND 2C 24AWG, AMA BRAID 64% SHIELDING WITH DRAIN WIRE,OD 4.5mm,JACKET BEIGE,DRAWING No.EUAB2801P2402C-139	L-25mm	M304
2	USB B MALE 2.0, GOLD PLATING 30u" ON CONTACTS, WHITE INSULATOR, SHORT TYPE	1set	M108
1	USB A MALE 2.0, GOLD PLATING 30u" ON CONTACTS, WHITE INSULATOR, SHORT TYPE	1set	M108
No.	DESCRIPTION	Q'TY	Supplier

APPROVED		MSL ENTERPRISES CORP.	Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm			
CHECKED	TIAN					
DRAWING	LIANG					
DATE	22/NOV/07	ITEM NO.	9461-16	UNIT:mm		

CHECKED