

OBSOLETE- USE PK-12N40PQ**Specificat**

Resonant Frequency (Hz)	4100 ± 500
Operating Voltage (Vdc)	3 ~ 15
Rated Voltage (Vdc)	12
Current Consumption Max. (mA)	10 at Rated Voltage
Sound Pressure Level Min. (dB)	83 at 10cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 707 UL94HB plastic resin (Color: Black)
Leading Pins	Tin Plated Brass
Weight (Grams)	0.8
Options	For other options contact factory

Dimensions: (units: mm)