



Dimensions: mm (In.)

SPECIFICATIONS	
Rating:	20A 250VAC
Contact Resistance:	50m Ω max.
Insulation Resistance:	500VDC 100M Ω min.
Dielectric Strength:	1500VAC, 1 minute
Material:	Housing & Cover, nylon
	Terminals, silver plated brass