


Compression Terminal 4

151-CJ9007

KOBICONN

Compression Terminal 4



SPECIFICATIONS

Contact Resistance:	30m Ω max.
Insulation Resistance:	100M Ω min.
Withstand Voltage:	There shall be no burn caused by short circuit and insulation construction.
Temperature Increase:	30°C max. (DC 4A)

Dimensions: mm (IN.)

No.	Part Name	Material	Disposal
1	Insulation Set	A.B.S. PA-757	94HB
2	Knob Handling	A.B.S. PA-757	94HB
3	Terminal-L	C2680R-H	Plated Sn-Cu
4	Terminal-S	C2680R-H	Plated Sn-Cu
5	Spring	SUS	-

Date Last Revised: 2-4-05

KC- 300268

151-CJ9007