



Date	Rev.	Description

**SPECIFICATIONS:**

1. CIRCUIT: A: (ON) -OFF
2. RATING: 1A250VAC/3A 125VAC
3. CONTACT RESISTANCE: 30mΩ MAX
4. INSULATION RESISANCE: DC 500V 100MΩ Min
5. DIELECTRIC STRENGTH: AC 1000V 1 MINUTE
6. ELECTRICAL LIFE: 6000 CYCLE Min
7. MECHANICAL LIFE: 10.000 CYCLE Min
8. TERMINAL MATERIAL: COPPER, ALLOY, (SILVER OR GOLD) , PLATED
9. PUSH FORCE: >0.3kg
10. BUTTON COLOR: RED, BLACK

TOLERANCE
±0.5
X. ± 0.5
.X ± 0.2
.XX ± 0.02

DCC. NO.
A4 DRAWING NO.

MATERIAL		<b>GOLDSUN ELECTRONICS CO., LTD.</b>			
		JAMECO NO.	2238186	GOLDSUN NO.	GR18-29A-B
DRAWN: Tina		Description			Rev.
VERIFY PEOPLE: Chesley		SPST Momentary Pushbutton Switch Black			1
UNIT:	mm	SCALE:	SHEET 1 OF 1	CAS No:	ERN No: