

**Consolidated Electronic Wire & Cable**

11044 King St

Franklin Park, IL 60131 US

**Phone:** 847-455-8830 **Fax:** 847-455-8837**Toll-free:** 800-621-4278**Email:** info@conwire.com **Website:** http://www.conwire.com**Part # 901, 30 AWG Solid Silver Plated Copper Wire Kynar Insulated UL Style 1423, Consolidated Hook Up Wire****30 AWG Solid Silver Plated Copper Wire Kynar Insulated UL Style 1423, Consolidated Hook Up Wire****Product Construction****Conductor:**

- 30 AWG Solid Silver Plated Copper Wire Conductor OFHC

**Insulation:**

- (900 series) color coded Kynar insulation
- Temperature -40°C to +105°C

**Applications:**

- Hook-Up wire
- Point to point wiring
- Printed circuit board wiring

**Industry Approvals:**

- UL Style 1423
- RoHS Compliant

**Packaging:**

- 1000 ft. spools
- 100 ft. spools
- Also available on bulk reels

**Note:** KYNAR® (PVDF Polyvinylidene Fluoride) is a trademark of Pennwalt Corp.**SPECIFICATIONS**

Gauge	30 AWG
Strands	Solid Silver Plated Copper Wire
Insulation Type	Kynar
Nominal Insulation Wall	0.004 in.
Nominal O.D.	0.020 in.
Color	0-Black/1-Brown/2-Red/3-Orange/4-Yellow/5-Green/6-Blue/7-Violet/8-Gray/9-White
Color Code Chart	Chart-Hook-Up Wire
UL Style	1423
Insulation Temperature	-40 to +105 °C