



**DIMENSIONS: mm (in.)**

**Electrical Specifications:**

- Rating: 10A / 125V AC, 6A / 250V AC
- Contact Resistance: 50mΩ Max.
- Insulation Resistance: 500VDC 100MΩ Min.
- Dielectric Strength: 1500V AC 1 minute



Shin Chin Part No.	Type	Circuit
R13-136B-05-BB	6P DPDT	On-On
<b>R13-136B-05-BR</b>	<b>6P DPDT</b>	<b>On-On</b>
R13-136C-05-BB	3P SPDT	On-On
R13-136C-05-BR	3P SPDT	On-On



**Rocker Switches**

R13-136B-05-BB, R13-136B-05-BR,  
R13-136C-05-BB, R13-136C-05-BR